

86mm Dia x 134mm FL Alum. Coated, Ellipsoidal Reflector



Precision Ellipsoidal Reflectors

Stock #68-797 3-4 DAYS

⊖ 1 ⊕ **€351,00**

ADD TO CART

Qty 1-10
€351,00

Qty 11+
€307,50

Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: 
BOROFLOAT®

Coating:
Protected Aluminum (400-700nm)

Coating Specification:
Ravg >85% @400 - 700nm

Coating Type: Metal
Center Hole Diameter (mm): 20.0
Height (mm): 46.0
Inner Diameter (mm): 81
Outer Diameter (mm): 86.00 +0.0/-0.5
Type: Specialty Mirror
Wavelength Range (nm): 400 - 700
Distance to Focal Point f_1 (mm) : 14
Distance to Focal Point f_2 (mm): 134

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
