

88mm Dia x 134mm FL Cold Mirror Coated, Ellipsoidal Reflector



Precision Ellipsoidal Reflectors

Stock #68-800 3-4 DAYS



1



€464,00

ADD TO CART

Qty 1-10

€464,00

Qty 11+

€406,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: BOROFLOAT®

Coating:
Cold Mirror, 0°

Coating Type:
Metal

Center Hole Diameter (mm): 20.0
Height (mm): 46.0
Inner Diameter (mm): 81
Outer Diameter (mm): 88.00 +0.0/-0.5
Type: Specialty Mirror
Distance to Focal Point f_1 (mm) : 14
Distance to Focal Point f_2 (mm): 134

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View