

9-90mm FL High Resolution Varifocal Lens



#68-668



Stock **#68-667** **7 In Stock**

- 1 + €504.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€504,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Day-Night **Note:**
Varifocal Lens **Type:**

Physical & Mechanical Properties

Length (mm):

93.00

Weight (g):

194.00

Diameter (mm):

45.00

Optical Properties

Field of View @ Min Working Distance (mm):

253 - 94

Horizontal Field of View, 1/2" Sensor:

41.1° - 4.2°

Focal Length Range (mm):

9-90

Working Distance (mm):

300 - ∞

Aperture (f/#):

f/1.8 - Closed

Lens Wavelength Range:

VIS

Sensor

Maximum Sensor Format:

1/2"

Threading & Mounting

Filter Thread:

M43 x0.75

Mount:

C-Mount

Regulatory Compliance

Reach 191:

[Compliant](#)

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Product Details

CS-Mount lenses are not compatible with C-Mount cameras.

- Low Distortion and Day/Night Options
- Focal Lengths from 4.4mm - 90mm
- C-Mount Versions

Megapixel Varifocal Lenses are the ideal choice when you need a specific field of view that corresponds to a non-standard focal length. They make system integration straightforward while allowing for fine tuning, and also create the flexibility so the lenses can be integrated across multiple applications. Day/Night varifocal lenses are the perfect choice when you need to extend your imaging system into the NIR without sacrificing visible imaging. Megapixel Varifocal Lenses have C-Mount versions. The lenses feature focal lengths from 4.4 to 90mm.