

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 9.0mm Dia. X -27 FL, Uncoated, Plano-Concave Lens



TECHSPEC Uncoated Plano-Concave (PCV) Lenses



Stock #45-384 3-4 DAYS

[Other Coating Options](#)

- 1 +

€29,00

ADD TO CART

Qty 1-9

€29,00

Qty 10+

€26,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm): -27.00
Substrate: N-SF11
f/#: 3.00
Numerical Aperture NA: 0.17
Coating: Uncoated
Type: Plano-Concave Lens
Wavelength Range (nm): 400 - 2500
Back Focal Length BFL (mm): -28.68
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 8.1
Edge Thickness ET (mm): 3.42
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -21.19
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 211: Compliant
Certificate of Conformance: View