

# 930nm CWL, 10nm FWHM, 25mm Mounted Diameter



Stock **#67-861** 3-4 DAYS

⊖ 1 ⊕ **€165,00**

ADD TO CART

|         |
|---------|
| Qty 1-9 |
| €165,00 |

|         |
|---------|
| Qty 10+ |
| €148,30 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.00 +0.00/-0.25

Angle of Incidence (°):  
0

Optical Density OD (Average):  
≥4.0

|                                                           |
|-----------------------------------------------------------|
| <b>Clear Aperture CA (mm):</b><br>21.0                    |
| <b>Center Wavelength CWL (nm):</b><br>930.00 +3.0/-1.0    |
| <b>Center Wavelength CWL Tolerance (nm):</b><br>+3.0/-1.0 |
| <b>Full Width-Half Max FWHM (nm):</b><br>10.00 ±2         |
| <b>Full Width-Half Max FWHM Tolerance (nm):</b><br>±2     |
| <b>Minimum Transmission (%):</b><br>>50                   |
| <b>Operating Temperature (°C):</b><br>-50 to +70          |
| <b>Coating:</b><br>Traditional Coated                     |
| <b>Surface Quality:</b><br>80-50                          |
| <b>Thickness Tolerance (mm):</b><br>±0.1                  |
| <b>Type:</b><br>Bandpass Filter                           |
| <b>Typical Applications:</b><br>General Filtering         |
| <b>Blocking Wavelength Range (nm):</b><br>200 - Far IR    |
| <b>Construction:</b><br>Mounted in Black Anodized Ring    |
| <b>Mount Thickness (mm):</b><br>5.9 ±0.1                  |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |