

TECHSPEC® 980nm CWL, 12.5mm Dia, 4.0 FWHM, Hard Coated Laser Clean-Up Filter



Stock **#68-857** ☐ In Stock

[Additional Bandwidths](#)



1



€95,70

ADD TO CART

Qty 1+

€95,70

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.1

Angle of Incidence (°):
0.00

Optical Density OD (Average):
≥4.0

Center Wavelength CWL (nm):
980.00

Design Wavelength DWL (nm): 980
Full Width-Half Max FWHM (nm): 4.00
Full Width-Half Max FWHM Tolerance (nm): ±1.5
Substrate: Fused Silica (Coming 7980)
Minimum Transmission (%): >80
Coating: Hard Coated
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Blocking Wavelength Range (nm): 850 - 970 & 990 - 1300
Clear Aperture (%): >90
Transmitted Wavefront, RMS: <i>N</i>4
Parallelism (arcsec): <30
Angle of Incidence Tolerance (°): ±5.0
Mount Thickness (mm): 3.5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View