

[See all 4 Products in Family](#)

9mm Dia. x 36mm FL, Commercial Grade, Plano-Convex Lens



Stock #23-072 CLEARANCE **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €20⁵⁰

ADD TO CART

Volume Pricing	
Qty 1+	€20,50 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Convex Lens **Type:**

Physical & Mechanical Properties

9.00 +0.00/-0.10 **Diameter (mm):**

6.00 **Centering (arcmin):**

Center Thickness CT (mm):

1.70

Edge Thickness ET (mm):

1.15

Clear Aperture CA (mm):

≥7.65

Optical Properties

Effective Focal Length EFL (mm):

36.00

Back Focal Length BFL (mm):

34.89

Coating:

Uncoated

Substrate: □

[N-BK7](#)

Focal Length Tolerance (%):

±1

Radius R_1 (mm):

18.61

f#:

4.00

Numerical Aperture NA:

0.13

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Feature Standard Designs and Specifications
- Also Available with [MgF₂ Coating](#)
- For More Options, View [Precision Quality Plano-Convex \(PCX\) Lenses](#)

Plano convex lenses (PCX) have one flat and one outward curving face and a positive focal length. They are ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. Commercial Grade Uncoated Plano-Convex (PCX) Lenses offer commercial quality, at an affordable price.

Technical Information

