

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

9mm Dia. x 9mm FL, Commercial Grade, Double-Convex Lens



Stock #27-728 CLEARANCE 3-4 DAYS

- 1 + €14,95

ADD TO CART

Qty 1+

€14,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
9.00 +0.00/-0.10

Back Focal Length BFL (mm):
7.86

Effective Focal Length EFL (mm):
9.00

Coating:
Uncoated

Substrate: ☐
N-SK18

Centering (arcmin): 6.00
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 1.53
Radius R ₁ (mm): 10.77
Clear Aperture CA (mm): ≥7.65
f##: 1.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.5
Type: Double-Convex Lens
Wavelength Range (μm): 0.38 - 2.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View