

TECHSPEC[®] C-Mount, 35mm Sq. x 3mm Thick Plate Mount



Mount Only (no optics included) for any 35mm sq x 3mm Thick Plate, #56-265

Stock **#56-265** 6 In Stock

-

1

+

€292⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€292,00 each
Qty 5-9	€257,70 each
Qty 10-25	€237,20 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Function:

Optic Mount (Fixed)

Type of Optics:

Square

Note:

Includes one C-Mount Aperture Cap ([#55-245](#))

Dimensions of Compatible Optics (mm):	
35.0 Sq.	
Physical & Mechanical Properties	
Dimensions (mm):	
38.0 x38.8 x50.0	
Extension Length (mm):	
38.0	
Min. Thickness of Compatible Optics (mm):	
3.00	
Max. Thickness of Compatible Optics (mm):	
6.00	
Threading & Mounting	
Thread Type:	
C-Mount	
Compatible Post:	
¼-20	
Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- ¼-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: [#11-139](#) and [#11-142](#) each include one S-Mount Aperture Cap ([#11-137](#))

Technical Information

