

Pro 360 Digital Protractor, 0.1 Degree Resolution

See More by [Mitutoyo](#)



Stock #78-356 **1 In Stock**

⊖ 1 ⊕ €357⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€357,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

0 - 360° **Range:**

950-317 **Model Number:**

Physical & Mechanical Properties

0.1 **Repeatability (°):**

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- English and Metric Units
- Stainless Steel Construction
- High Measurement Resolution

Mitutoyo Pocket Rulers and Protractors are ideal tools for quick and accurate manual measurements in optical settings to maintain system performance. These Pocket Rulers feature a sliding stop for accurate measurements, are non-magnetic to prevent interference with sensitive applications, and feature a conversion chart on the back between inch divisions and millimeters. Protractors are available in four form factors to best match the application including digital, universal bevel, semi-circular base, and rectangular base. Mitutoyo Pocket Rulers and Protractors are made from stainless steel making them stronger than aluminum to maintain straightness and prevent distortion.
