

[See all 3 Products in Family](#)

## Achromatic Lens 6.25mm Dia. x 35mm FL, Uncoated



Stock #32-306 **CLEARANCE** 7 In Stock

⊖ 1 ⊕ €13<sup>50</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€13,50 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Achromatic Lens **Type:**

### Physical & Mechanical Properties

2.30 **Center Thickness CT 1 (mm):**

0.90 **Center Thickness CT 2 (mm):**

6.2500000000 +0.00/-0.05 **Diameter (mm):**

2.86 **Edge Thickness ET (mm):**

±0.1 **Center Thickness Tolerance (mm):**

1.00 **Centering (arcmin):**

## Optical Properties

33.59 **Back Focal Length BFL (mm):**

Uncoated **Coating:**

35.0000000000 **Effective Focal Length EFL (mm):**

[N-BK7 / N-SF5](#) **Substrate:**

0.0800000000 **Numerical Aperture NA:**

23.1400000000 **Radius R<sub>1</sub> (mm):**

-14.51 **Radius R<sub>2</sub> (mm):**

-38.86 **Radius R<sub>3</sub> (mm):**

40-20 **Surface Quality:**

±2 **Focal Length Tolerance (%):**

632.8 **Focal Length Specification Wavelength (nm):**

5.6 **f#:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Discounts up to 80% Off
- Quantities Extremely Limited
- Final Sale, No Returns

Shop the EO Mega Clearance presentations for the hottest deals on component-level products. Quickly browse the best optics, [imaging](#), and [photonics](#) deals you will ever see. Quantities are extremely limited and are sold on a first-come-first-serve basis.

Hurry, while supplies last. EO Mega Clearance products will never be sold again. Check out our standard [clearance products](#) for even more deals!

All products are final sale; EO will not accept returns. No additional information is available other than what is listed.

## Compatible Mounts