

[See all 14 Products in Family](#)

AI Red 625nm LED Pattern Projector

See More by [Advanced Illumination](#)



Stock **#87-449** **3 In Stock**

-

1

+

€775⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€775,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
SL191-625IC	Model Number:
50,000	LED Lifetime (hours):
LED Illuminator	Type of Illumination:
Note:	

Optional Manual Intensity Adjustment #86-887 and #89-555 are Available	
Advanced Illumination	Manufacturer:
Spot Light	Geometry:
Constant	Illumination Mode:
Physical & Mechanical Properties	
20.8	Diameter of Compatible Reticle (mm):
Optical Properties	
Red	Color:
625	Wavelength (nm):
Hardware & Interface Connectivity	
Flying Leads	Connector:
Power Supply: Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 233:

Product Details

- Multiple Wavelength Options Available
- Equip C-Mount [Imaging Lenses](#) to Control Illumination Geometry
- Ideal for 3D Reconstruction and Mapping

Advanced Illumination LED Pattern Projectors are compact illuminators designed for applications requiring structured illumination. These illuminators can be used with any C-mount compatible imaging lens and negatively patterned 21mm reticle to achieve specific structured illumination geometries. When used without a reticle, these illuminators can be adjustable spotlights. Advanced Illumination LED Pattern Projectors are ideal for 3D reconstruction and mapping. The illuminators are available in blue, green, red or white.

Note: [Power supply](#) and C-mount [imaging lens](#) are required and sold separately.</>

Technical Information



