

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

See More by [Allied Vision](#)



Allied Vision Alvium USB 3.1 Cameras



Stock #19-567 [CONTACT US](#)

[Similar Cameras](#)

-

1

+

€725,00

ADD TO CART

Qty 1+

€725,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
USB 3.1 Gen 1

Type: Monochrome Camera
Manufacturer: Allied Vision
Mounting Threads: ¼-20 and M6 with Tripod Mount Adapter #14-156
Image Buffer: 256KB
Camera Family: Alvium
Model Number: 1800 U-511m
Imaging Sensor: Sony IMX547
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/1.8"
Resolution (MegaPixels): 5.10
Pixels (H x V): 2,464 x 2,064
Pixel Size, H x V (µm): 2.74 x 2.74
Sensing Area, H x V (mm): 6.8 x 5.7
Frame Rate (fps): 66.00
Pixel Depth: 8/10/12 bit
Exposure Time: 164µs - 10s @ 450 MBps 163µs - 10s @ 200 MBps
Connector: USB 3.1 Gen 1, Micro-B
Power Supply: Power over USB or via GPIO
Power Consumption (W): 3.2
GPIOs: 4 Programmable TTL GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 25 x 29 x 29 (includes connectors and lens mount)
Weight (g): 45
Mount: CS-Mount
Housing: Partial
Interface Port Orientation: Back Panel
Operating Temperature (°C): -20 to +65 (housing temperature)
Storage Temperature (°C): -20 to +85
GPIO Connector Type: 7-pin JST
Machine Vision Standard: USB3 Vision v1.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant