

Allied Vision Manta G-145 2/3" Monochrome CCD Camera

See More by [Allied Vision](#)



Allied VSION Manta GigE Cameras (Front)



Stock **#68-579** [CONTACT US](#)

[Similar Cameras](#)

- 1 + **€2.251,00**

ADD TO CART

Qty 1+

€2.251,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE

Type:
Monochrome Camera

Manufacturer: Allied Vision
Mounting Threads: ¼-20 with Tripod Mount Adapter #89-996
Image Buffer: 32MB
Camera Family: Manta
Model Number: Manta G-145B
Imaging Sensor: Sony ICX285
Type of Sensor: Progressive Scan CCD
Type of Shutter: Global
Camera Sensor Format: 2/3"
Resolution (MegaPixels): 1.40
Pixels (H x V): 1,360 x 1,024
Pixel Size, H x V (µm): 6.45 x 6.45
Sensing Area, H x V (mm): 8.5 x 7.1
Frame Rate (fps): 15.00
Pixel Depth: 12 bit
Exposure Time: Via Software
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power Supply Required and Sold Separately. USA: #15-281 Europe: #15-281 Japan: #15-281 China: #15-281
Power Consumption (W): 3.7 (12VDC External Power Supply)
GPIOs: 2 opto-isolated inputs, 2 opto-isolated outputs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 71 x 44 x 29 (excludes connectors and lens mount)
Weight (g): 200
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 64.3
Operating Temperature (°C): +5 to +45
Storage Temperature (°C): -10 to +70
GPIO Connector Type: 12-pin Hirose (HR10)
Machine Vision Standard: GigE Vision v1.2, GenICam SFNC V1.2.1

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

