

Basler Ace acA4024-29uc USB 3.0 Color Camera



Stock **#37-216** 3-4 DAYS

[Similar Cameras](#)



1



€529,00

ADD TO CART

Qty 1+

€529,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
USB 3.0

Type:
Color Camera

Manufacturer:
Basler

Mounting Threads: ¼-20 with Tripod Mount Adapter #88-517
Image Buffer: Not Specified
Camera Family: ace
Model Number: acA4024-29uc
Imaging Sensor: Sony IMX226
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Rolling
Camera Sensor Format: 1/1.7"
Resolution (MegaPixels): 12.00
Pixels (H x V): 4,024 x 3,036
Pixel Size, H x V (µm): 1.85 x 1.85
Sensing Area, H x V (mm): 7.44 x 5.62
Frame Rate (fps): 31.00
Pixel Depth: 10/12 bit
Exposure Time: Programmable via camera API
Connector: USB 3.0, Micro-B with Screw Locks
Power Supply: Power over USB
Power Consumption (W): 3
GPIOs: 1 opto-coupled input line, 1 opto-coupled output line, 2 general purpose I/O (GPIO) lines
Synchronization: Hardware Trigger (GPIO), Software Trigger, or Free-Run
Dimensions (mm): 29.3 x 29 x 29 (excludes connectors and lens mount)
Weight (g): 80
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): Not Specified
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 6-pin Hirose (HR10)
Machine Vision Standard: USB3 Vision v1.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant