

[All Products](#) / [Cameras](#) / [USB Cameras](#) / [Basler ace USB 3.0 Cameras](#)

[See all 59 Products in Family](#)

Basler ace acA800-510um Monochrome USB 3.0 Camera

See More by [Basler](#)



Basler ace USB 3.0 Cameras (Front)



Stock **#33-976** [CONTACT US](#)

-

1

+

€489⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€489,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

SPECIFICATIONS

General

Monochrome Camera	Type:
acA800-510um	Model Number:
Basler	Manufacturer:
ace	Camera Series:
Monochrome	Spectrum:

Physical & Mechanical Properties

29.3 x 29 x 29 (excludes connectors and lens mount)	Dimensions (mm):
80	Weight (g):
Full	Housing:

Sensor

Not Specified	Image Buffer:
1/3.6"	Sensor Format:
0.50	Resolution (Megapixels):
511.00	Frame Rate (fps):
800 x 600	Pixels (H x V):
4.8 x 4.8	Pixel Size, H x V (µm):
3.84 x 2.88	Sensing Area, H x V (mm):
ON Semi PYTHON 500	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
10 bit	Pixel Depth:
Freely Programmable	Exposure Time:
56.3	Dynamic Range (dB):
USB3 Vision v1.0	Machine Vision Standard:

Electrical

3	Power Consumption (W):
---	------------------------

Hardware & Interface Connectivity

USB 3.0	Interface:
USB 3.0, Micro-B with Screw Locks	Connector:
Power over USB	Power Supply:
1 opto-coupled input line, 1 opto-coupled output line, 2 general purpose I/O (GPIO) lines	GPIOs:
Hardware Trigger (GPIO) or Free-Run	Synchronization:
Back Panel	Interface Port Orientation:
6-pin Hirose (HR10)	GPIO Connector Type:
Software Driver: Windows 32 and 64 bit, Linux, OS X	Operating System:

Threading & Mounting

	Mount:
--	--------

C-Mount

Mounting Threads:
1/4-20 with Tripod Mount Adapter [#88-517](#)

Environmental & Durability Factors

Operating Temperature (°C):
0 to +50

Storage Temperature (°C):
-20 to +80

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)

PRODUCT DETAILS

- High Speed USB 3.0 Interface
- Ultra-Small Form Factor
- Fully USB3 Vision Compliant

Basler ace USB 3.0 Cameras are an ideal choice for analog camera users looking to upgrade to digital, or for FireWire or USB 2.0 users looking for faster data transfer rates. Basler ace USB 3.0 Cameras are fully USB3 Vision compliant and feature a small, 29 x 29mm form factor that makes them easy drop-in replacements for many analog, FireWire, or USB 2.0 cameras. Additionally, these USB 3.0 cameras feature screw-locking USB 3.0 ports for increased ruggedness in demanding applications, such as factory floor use. All cameras include the Basler Pylon SDK software and driver.

TECHNICAL INFORMATION

