

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

Bench Mounted Laser Detection Head UV



Bench Mounted Laser Detection Head UV, #55-296

Stock #55-296 3-4 DAYS



1



€225,00

ADD TO CART

Qty 1+
€225,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Active Area Diameter (mm):
35.00

Outer Diameter (mm):
70.00

Thickness (mm):
8.00

Type:
Detection Head

Wavelength:

UV
Typical Applications: HeCd, Ar-Ion, tripled Nd:YAG, etc.
Persistence (Stimulation Removed): 6 s - 4 min (dependent on ambient light)
Emission Color: Yellow (580nm), Broadband (490 - 700nm)
Stimulation Range: 250 - 550nm
Minimum Stimulation, Continuous: <1 nW/cm ² @ 365nm & 450nm
Minimum Stimulation, Pulsed: <8 W/cm ² @ 337nm, 4ns, 20Hz <40 W/cm ² @ 337nm, 4ns, 1Hz
Maximum Stimulation, Continuous: 100 W/cm ² @ 512nm
Maximum Stimulation, Single Pulse: 850 MW/cm ² @ 337nm, 4ns 60 MW/cm ² @ 1064nm, 7ns

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View