

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Mounted Machine Vision Filters

Stock #21-503 3-4 DAYS



1



€535,00

ADD TO CART

Qty 1-9

€535,00

Qty 10+

€508,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Blocking Wavelength Range (nm):
200-400, 550-1206

Clear Aperture CA (mm):
81.70

Coating:
Hard Coated

Filter Thread: M86 x0.75
Color: Blue
Center Wavelength CWL (nm): 470.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 85.00
Mount Thickness (mm): 6.1
Mount Thickness Including Threads (mm): 8.3
Outer Diameter (mm): 89.00
Substrate Thickness (mm): 1.8
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
