

TECHSPEC® 30mm, C-Mount Ring Mount, 1/4-20 Tapped Hole



Stock #52-930 **2 In Stock**

- 1 + €110^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€110,00 each
Qty 5-9	€97,40 each
Qty 10-25	€90,20 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Post Mounting Adapter **Function:**

Physical & Mechanical Properties

Black Anodized Aluminum (6061 T6) **Construction:**

48.0 **Outer Diameter (mm):**

Thickness (mm):

12.70

Inner Diameter (mm):

30.0

Threading & Mounting

Thread Type:

C-Mount

Mounting Flat to Center (mm):

21.75

Compatible Post:

1/4-20

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Compliant](#)

Product Details

- Allow for Post Mounting C, S, and T-Mount Tube System Assemblies
- 1/4-20 or M6 Tapped Mounting Options
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Ring Mounts feature a screw closure and accept 30mm, 16mm, and 48mm outer diameter tubes and barrels, respectively. Ring mounts are available with either 1/4-20 or M6 tapped mounting threads with a flat mounting surface to facilitate mounting to optical bench posts. These mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads. TECHSPEC C, S, and T-Mount Ring Mounts are ideal for quickly integrating C, S, or T-Mount tube assemblies into any benchtop system. A black anodized construction reduces reflections within a system.

Technical Information

