

TECHSPEC® C-Mount Extension Tube Kit



Stock #54-668 **4 In Stock**

- 1 + €367.⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	€367,00 each
Qty 5-9	€323,70 each
Qty 10-25	€298,10 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

C-Mount Kit **Type:**

Extension Tube (Fixed) **Function:**

Contents of Kit:

5mm: #54-628, 10mm: #54-629, 15mm: #54-630,
50mm: #54-632, 100mm: #54-633

Physical & Mechanical Properties

22.0 **Clear Aperture CA (mm):**

30.0 **Outer Diameter (mm):**

Threading & Mounting

C-Mount **Thread Type:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 235:**

Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

Technical Information

