

[See all 10 Products in Family](#)

CentriMax™ Large Format Adapter (for up to 4/3" sensors)



#63-025: CentriMax™ Large Format Adapter (for up to 4/3" sensors)

Stock #63-025 [CONTACT US](#)

⊖ 1 ⊕ €835⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€835,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Lens Accessory **Type:**

Threading & Mounting

M42 x 0.75 (T-Mount) **Mount:**

Regulatory Compliance

Compliant

RoHS 2015:

Compliant

Reach 224:

[View](#)

[Certificate of Conformance:](#)

Product Details

- CentriTel® Internal Focusing System for Constant Magnification
- Focuses from 3000mm to 60mm with MX-Series Objectives
- Can be Equipped with Infinity-corrected Microscope Objectives
- Coaxial In-line Illuminator (Optional) for Reflective Objects

CentriMax™ can be actively focused anywhere from 3000mm to 60mm by using supplemental MX-Series objectives. Once a working distance is chosen, its patented CentriTel® internal focusing system allows for focusing from top to bottom of objects without change in magnification. Unlike InfiniMax™, CentriMax™ does not need physical movement to maintain magnification by a resetting of the focus. Rather, the CentriTel® internal focusing system maintains constant magnification during focal translation. Depth details peel away, yet magnification remains essentially constant. CentriMax™ is perfect for z-sectioning and making measurements from a fixed position. This lens also features a variable iris diaphragm for increased depth of field without altering CentriTel® characteristics. Other accessories include: supplemental adapters (transmitted or coaxial) for use with Achrovid™, Mitutoyo, Edmund, Olympus, or Nikon infinity corrected objectives.

Technical Information

Objective	Working Distance	Magnification	Field of View, FOV
MX-LR (#86-894)	3000mm	0.11X	7.0mm
	1330mm	0.25X	8.1mm
	530mm	0.58X	14.0mm
MX-1 (#56-014)	310mm	0.96X	7.0mm
	400mm	0.83X	8.1mm
	690mm	0.48X	14.0mm
MX-2 (#56-015)	240mm	1.22X	5.5mm
	295mm	1.12X	6.0mm
	425mm	0.74X	9.0mm
MX-3 (#56-016)	175mm	1.76X	3.8mm
	218mm	1.49X	4.5mm
	273mm	1.12X	6.0mm
MX-4 (#56-017)	165mm	1.91X	3.5mm
	190mm	1.68X	4.0mm
	238mm	1.34X	5.0mm
MX-5 (#56-018)	130mm	2.23X	3.0mm
	145mm	2.09X	3.2mm
	175mm	1.68X	4.0mm
MX-6 (#56-019)	60mm	4.47X	1.5mm
	65mm	4.47X	1.5mm
	70mm	4.19X	1.6mm