

Preloaded Norland Optical Adhesive NOA 65 Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#55-087** ☐ In Stock

1 **€32,50**

ADD TO CART

Qty 1-4

€32,50

Qty 5+

€31,40

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Size (oz):
0.34

Size (cc):
10.00

Glass Bonding:
Good

Metal Bonding: Good
Plastic Bonding: Fair
Viscosity (cps): 1200
Durability: Flexible
Index of Refraction n_d: 1.52 @ 589nm
Norland Number: 65
Shelf Life: 6 months
Type: Barrel
Typical Applications: More flexible adhesive for extra low strain applications. Suitable for cold blocking applications.
Note: Contains 10g of adhesive
Absorption Range (nm): 350 - 380
Bonding Type: Glass to Glass/Metal
Energy for Full Cure (J/cm²): 4.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
