

TECHSPEC® 30mm ID Kinematic Cage Mounting Plate



#85-663

Stock **#85-663 1 In Stock**

- 1 + €180⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€180,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Tip-Tilt **Function:**

Circular/Cylindrical Tube **Type of Optics:**

Physical & Mechanical Properties

30.0 **Plate Inner Diameter (mm):**

Bolt Circle Diameter for 6mm Dia. Thru (mm):

38.0

Outer Diameter (mm):

50.0

Construction:

Black Anodized Aluminum

Dimensions (mm):

50 Dia.

Thickness (mm):

32.00

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 235:

[Compliant](#)

Product Details

- Specialized Plates Designed to Hold and Position Optics
- Anodized Aluminum Construction with Stainless Steel Screws
- X-Y Micro Positioning Plate with RMS Mounting Thread

TECHSPEC® Cage System Adjustable Plates are used to integrate optical components into the TECHSPEC Cage System while providing rotary, tip-tilt, or linear adjustment. Rotary Mounts are available with M6 or 1/4-20 mounting threads and are designed to fit within the inner diameter of 25mm [cage system plates](#). The Kinematic Cage Mounting Plate is compatible with 30mm [cage system plates](#) and enables kinematic adjustment of cage system assemblies. The X-Y Micro Position Stage Plate also has 6mm rod holes, and features a 7mm clear aperture, X-Y micro-positioner, and an RMS threaded mount for precision mounting alignment.