

[See all 4 Products in Family](#)

TECHSPEC[®]

30mm ID Kinematic Cage Mounting Plate



#85-663

Stock **#85-663** 1 In Stock

-

1

+

€180⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€180,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Tip-Tilt	Function:
Circular/Cylindrical Tube	Type of Optics:

Physical & Mechanical Properties

30.0	Plate Inner Diameter (mm):
	Bolt Circle Diameter for 6mm Dia. Thru (mm):

38.0	
	Outer Diameter (mm):
50.0	
	Construction:
Black Anodized Aluminum	
	Dimensions (mm):
50 Dia.	
	Thickness (mm):
32.00	

Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 235:
Compliant	

Product Details

- Specialized Plates Designed to Hold and Position Optics
- Anodized Aluminum Construction with Stainless Steel Screws
- X-Y Micro Positioning Plate with RMS Mounting Thread

TECHSPEC® Cage System Adjustable Plates are used to integrate optical components into the TECHSPEC Cage System while providing rotary, tip-tilt, or linear adjustment. Rotary Mounts are available with M6 or 1/4-20 mounting threads and are designed to fit within the inner diameter of 25mm [cage system plates](#). The Kinematic Cage Mounting Plate is compatible with 30mm [cage system plates](#) and enables kinematic adjustment of cage system assemblies. The X-Y Micro Position Stage Plate also has 6mm rod holes, and features a 7mm clear aperture, X-Y micro-positioner, and an RMS threaded mount for precision mounting alignment.