

# Hoya G545 (VIS) 12mm Dia., Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#34-439** 3-4 DAYS

- 1 + **€45,00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| €45,00                        |
| Qty 11+                       |
| €40,00                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
12.00

Center Wavelength CWL (nm):

|                                                             |
|-------------------------------------------------------------|
| 545.00                                                      |
| <b>Density (g/cm³):</b><br>3.10                             |
| <b>Full Width-Half Max FWHM (nm):</b><br>47.00              |
| <b>Glass/Filter Number:</b><br><a href="#">Hoya G545</a>    |
| <b>Substrate:</b> <input type="checkbox"/><br>Colored Glass |
| <b>Coating:</b><br>Uncoated                                 |
| <b>Color:</b><br>Green                                      |
| <b>Surface Quality:</b><br>80-50                            |
| <b>Thickness (mm):</b><br>2.50                              |
| <b>Thickness Tolerance (mm):</b><br>±0.2                    |
| <b>Type:</b><br>Bandpass Filter                             |
| <b>Wavelength:</b><br>VIS                                   |
| <b>Parallelism (arcmin):</b><br>≤1                          |
| <b>Dimensional Tolerance (mm):</b><br>+0/-0.25              |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Reach 224:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |