

[See all 3 Products in Family](#)

Adjustable Grating Mount Adapter for 40-60mm Optic



Stock #18-539 **4 In Stock**

- 1 + €202⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	€202,00 each
Qty 10+	€192,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Fixed **Type:**

Square or Rectangular **Type of Optics:**

Includes Hex Wrench for Locking Screws **Note:**

Compatible Kinematic Mount:
[#15-866](#), [#58-851](#), [#58-854](#)

Threading & Mounting

Size of Compatible Optics (mm):
40.0 - 60.0

Regulatory Compliance

Compliant **RoHS 2015:**

[View](#) **Certificate of Conformance:**

Compliant **Reach 247:**

Product Details

- Mount up to 60mm Tall Diffraction Gratings
- Easy Adjustment via Side Locking Screws
- Designed for Integration into 25.4mm Diameter Optic Mounts

Adjustable Grating Mounts are designed to hold diffraction gratings without damaging their sensitive grating surface. Featuring a 3-point mounting style with spring and metal contacts, these mounts provide adequate clamping pressure while allowing for easy adjustment via side locking screws. A 25.4mm diameter extension on the rear of the mount allows for integration into [TECHSPEC® Kinematic Mounts](#), [E-Series Circular Kinematic Mounts](#), and [fixed mirror mounts](#). Adjustable Grating Mounts can be adjusted to accommodate a range of grating sizes, up to 60mm in height.