

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #18-786 ☐ In Stock

☐ [Additional Bandwidths](#)



1



€37,00

ADD TO CART

Qty 1-10

€37,00

Qty 11+

€33,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00

Center Wavelength CWL (nm): 830.00
Density (g/cm³): 2.75
Full Width-Half Max FWHM (nm): 260.00
Glass/Filter Number: Hoya RT830
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Black
Surface Quality: 60-40
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Wavelength: IR
Parallelism (arcmin): ≤1
Dimensional Tolerance (mm): ±0.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View