

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #18-770 3-4 DAYS



1



€169,00

ADD TO CART

Qty 1-10

€169,00

Qty 11+

€149,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
50.80 x 50.80

Center Wavelength CWL (nm):

340.00
Density (g/cm³): 2.92
Full Width-Half Max FWHM (nm): 85.00
Glass/Filter Number: Hoya U340
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Black
Surface Quality: 60-40
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Wavelength: UV
Parallelism (arcmin): ≤2
Dimensional Tolerance (mm): ±0.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
