

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #18-806 3-4 DAYS



1



€88,00

ADD TO CART

Qty 1-10

€88,00

Qty 11+

€78,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
50.8 x 50.8

Cut-On Wavelength (nm):
300.00 ±7

Density (g/cm³):
2.50

Glass/Filter Number: Hoya UV30N
Substrate: Colored Glass
Coating: Uncoated
Color: Clear
Surface Quality: 60-40
Transformation Temperature (°C): 533
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed
Δλ (nm): <40
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View