

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #18-867 3-4 DAYS



1



€88,00

ADD TO CART

Qty 1-10

€88,00

Qty 11+

€78,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00

Cut-On Wavelength (nm):
480.00 ±5

Density (g/cm³):
2.67

Glass/Filter Number: Hoya Y48	
Substrate: ☐ Colored Glass	
Coating: Uncoated	
Color: Yellow	
Surface Quality: 60-40	
Transformation Temperature (°C): 560	
Thickness (mm): 1.00	
Thickness Tolerance (mm): ±0.1	
Type: Longpass Filter	
Wavelength: VIS	
Dimensional Tolerance (mm): ±0.2	
Reflection Factor P _d : 0.92	
Bevel: Protective as needed	
Δλ (nm): <25	
TH (%): >85	

Regulatory Compliance

RoHS: Compliant	
Certificate of Conformance: View	