

[See all 53 Products in Family](#)

IDS GV-5250FA-C-HQ, GigE, 1/1.8" Color Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ FAIP65/67 PoE Cameras (Front)



Stock **#26-298** **1 In Stock**

-

1

+

€920^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€920,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads	
Color	Spectrum:
General	
Color Camera	Type:
GV-5250FA-C-HQ	Model Number:

IDS Imaging Development Systems	Manufacturer:
uEye+ FA	Camera Series:
Physical & Mechanical Properties	
41 x 53 x 42.7 (excludes connectors and lens mount)	Dimensions (mm):
173	Weight (g):
Full	Housing:
Sensor	
128MB	Image Buffer:
1/1.8"	Sensor Format:
1.92	Resolution (Megapixels):
52.00	Frame Rate (fps):
1,600 x 1,200	Pixels (H x V):
4.50 x 4.50	Pixel Size, H x V (µm):
7.2 x 5.4	Sensing Area, H x V (mm):
e2v EV76C570	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Rolling / Global / Global Start	Shutter Type:
10 bit	Pixel Depth:
0.02ms - 181ms	Exposure Time:
66.00	Dynamic Range (dB):
GigE Vision	Machine Vision Standard:
Electrical	
1.7 - 2.4	Power Consumption (W):
Hardware & Interface Connectivity	
GigE (PoE)	Interface:
GigE M12, screwable	Connector:
Power over Ethernet (PoE) or 12 - 24VDC via GPIO with #19-692	Power Supply:
2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Voltage Output, 1 Ground	GPIOs:
Hardware Trigger (GPIO); Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
8-pin Binder connector (Binder series 712: 09-0427-020-08)	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
¼-20 with Tripod Mount Adapter #19-694	Mounting Threads:
Environmental & Durability Factors	
0 to +55	Operating Temperature (°C):
	Storage Temperature (°C):

Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.