

[See all 103 Products in Family](#)

## IDS U3-3180CP-M-GL, USB 3.0, 1" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Camera, CP Model (Front)



Stock **#24-084** **2 In Stock**

⊖ 1 ⊕ €1.140<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€1.140,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

Monochrome **Spectrum:**

### General

Monochrome Camera **Type:**

U3-3180CP-M-GL **Model Number:**

IDS Imaging Development Systems **Manufacturer:**

uEye+ CP **Camera Series:**

## Physical & Mechanical Properties

29 x 29 x 29 (excludes connectors and lens mount) **Dimensions (mm):**

50 **Weight (g):**

Full **Housing:**

## Sensor

128MB **Image Buffer:**

1" **Sensor Format:**

5.30 **Resolution (Megapixels):**

73.00 **Frame Rate (fps):**

2,592 x 2,048 **Pixels (H x V):**

4.80 x 4.80 **Pixel Size, H x V ( $\mu\text{m}$ ):**

12.441 x 9.83 **Sensing Area, H x V (mm):**

ON Semi PYTHON 5000 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

10 bit **Pixel Depth:**

0.17ms - 500ms **Exposure Time:**

Not Specified **Dynamic Range (dB):**

USB3 Vision **Machine Vision Standard:**

## Electrical

1.6 - 4.3 **Power Consumption (W):**

## Hardware & Interface Connectivity

USB 3.0 **Interface:**

USB 3.0 micro-B, screwable **Connector:**

Power over USB **Power Supply:**

2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Output  
Supply Voltage, 1 Ground **GPIOs:**

Hardware Trigger (GPIO) **Synchronization:**

Back Panel **Interface Port Orientation:**

8-pin Hirose connector (HR25-7TR-8PA(73)) **GPIO Connector Type:**

## Threading & Mounting

C-Mount **Mount:**

1/4-20 with Tripod Mount Adapter [#16-017](#) **Mounting Threads:**

## Environmental & Durability Factors

0 to +55 **Operating Temperature ( $^{\circ}\text{C}$ ):**

-20 to +60 **Storage Temperature ( $^{\circ}\text{C}$ ):**

## Regulatory Compliance

[Exempt](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Contains SVHC\(s\)](#)

Reach 251:

## Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framerrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.