

[See all 103 Products in Family](#)

IDS U3-31N0CP-C-HQ, USB 3.0, 1.1" Color Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Cameras



Stock #78-113 **1 In Stock**

⊖ 1 ⊕ €1.840⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | €1.840,00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Color **Spectrum:**

General

Color Camera **Type:**

U3-31N0CP-C-HQ **Model Number:**

IDS Imaging Development Systems **Manufacturer:**

uEye+ CP **Camera Series:**

Physical & Mechanical Properties

29 x 29 x 29 (excludes connectors and lens mount) **Dimensions (mm):**

50 **Weight (g):**

Full **Housing:**

Sensor

128MB **Image Buffer:**

1.1" **Sensor Format:**

16.20 **Resolution (Megapixels):**

25.00 **Frame Rate (fps):**

5,328 x 3,040 **Pixels (H x V):**

2.74 x 2.74 **Pixel Size, H x V (µm):**

14.599 x 8.33 **Sensing Area, H x V (mm):**

Sony IMX542 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

12 bit **Pixel Depth:**

0.035ms - 2000ms **Exposure Time:**

70.00 **Dynamic Range (dB):**

USB3 Vision **Machine Vision Standard:**

Electrical

1.9 - 4.5 **Power Consumption (W):**

Hardware & Interface Connectivity

USB 3.0 **Interface:**

USB 3.0 micro-B, screwable **Connector:**

Power over USB **Power Supply:**

Hardware Trigger (GPIO); Software Trigger **Synchronization:**

Back Panel **Interface Port Orientation:**

8-pin Hirose connector (HR25-7TR-8PA(73)) **GPIO Connector Type:**

Threading & Mounting

C-Mount **Mount:**

1/4-20 with Tripod Mount Adapter [#35-088](#) **Mounting Threads:**

Environmental & Durability Factors

0 to +55 **Operating Temperature (°C):**

-20 to +60 **Storage Temperature (°C):**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **Reach 251:**

Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framerrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.

;