

[See all 103 Products in Family](#)

IDS U3-3990SE-M-GL, USB 3.0, 1.1" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Camera, SE Model (Front)



Stock #24-141 **2 In Stock**

⊖ 1 ⊕ €2.505⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€2.505,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Monochrome **Spectrum:**

General

Monochrome Camera **Type:**

U3-3990SE-M-GL **Model Number:**

IDS Imaging Development Systems **Manufacturer:**

uEye+ SE **Camera Series:**

Physical & Mechanical Properties

34 x 44 x 47 (excludes connectors and lens mount) **Dimensions (mm):**

110 **Weight (g):**

Full **Housing:**

Sensor

128MB **Image Buffer:**

1.1" **Sensor Format:**

20.30 **Resolution (Megapixels):**

19.00 **Frame Rate (fps):**

4,512 x 4,512 **Pixels (H x V):**

2.74 x 2.74 **Pixel Size, H x V (µm):**

12.363 x 12.363 **Sensing Area, H x V (mm):**

Sony IMX541 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

12 bit **Pixel Depth:**

0.013ms - 2000ms **Exposure Time:**

70.00 **Dynamic Range (dB):**

USB3 Vision **Machine Vision Standard:**

Electrical

1.9 - 5.8 **Power Consumption (W):**

Hardware & Interface Connectivity

USB 3.0 **Interface:**

USB Type-C, screwable **Connector:**

Power over USB **Power Supply:**

2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Voltage Output, 1 Ground **GPIOs:**

Hardware Trigger (GPIO); Software Trigger **Synchronization:**

Back Panel **Interface Port Orientation:**

8-pin Hirose connector (HR25-7TR-8PA(73)) **GPIO Connector Type:**

Threading & Mounting

C-Mount **Mount:**

¼-20 with Tripod Mount Adapter [#16-017](#) **Mounting Threads:**

Environmental & Durability Factors

0 to +55 **Operating Temperature (°C):**

-20 to +60 **Storage Temperature (°C):**

Regulatory Compliance

[Exempt](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Contains SVHC\(s\)](#)

REACH 241:

Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framerrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.