

InfiniGage UV Main Body

See More by [Infinity Photo-Optical Company](#)



Stock **#62-831** [CONTACT US](#)

- 1 + **€760,00**

ADD TO CART

Qty 1+

€760,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Wavelength Range (nm):
250 - 700

Wavelength Range (µm):
0.25 - 0.7

Type:
Fixed Magnification Lens

Primary Magnification PMAG:
Spacer Required

Maximum Sensor Format:

1/2"

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 224:
[Compliant](#)

Certificate of Conformance:
[View](#)