

Infiniprobe N-80 UV Right Angle Video Microscope

See More by [Infinity Photo-Optical Company](#)



Stock #59-121 [CONTACT US](#)

⊖ 1 ⊕ €4.965⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€4.965,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Long Distance Microscope **Type:**

UV, Right Angle **Style:**

Physical & Mechanical Properties

149.00 **Length (mm):**

Maximum Diameter (mm):

66.5

Weight (g):

184.3

Optical Properties

Horizontal Field of View, 2/3" Sensor:

1.1mm

Horizontal Field of View, 1/2" Sensor:

0.8mm

Primary Magnification PMAG:

0X- 8.0X

Working Distance (mm):

20 - ∞

Sensor

Maximum Sensor Format:

2/3"

Threading & Mounting

Mount:

C-Mount

Regulatory Compliance

RoHS 2015:

Compliant

Reach 224:

Compliant

Certificate of Conformance:

[View](#)


Product Details

- Available in Standard and Right Angle Versions
- Magnification Range from 0X to 8.0X
- Max 2/3" Sensor Format
- Direct Video C-Mount Coupling
- No Adapters Required

The InfiniProbe™ is available in a model designed to continuously focus UV light. The InfiniProbe™ 8.0X UV Video Microscope boasts a magnification range of 0-8X, supports up to a 2/3" format sensor, and offers direct video C-Mount coupling while incorporating exceptional resolution in the UV spectrum. Focusing from infinity down to a 0.8mm FOV at a WD of 20mm, the InfiniProbe™ 8.0X UV is capable of yielding magnifications up to 328X on a 13 inch monitor (based on a 1/2" sensor). To double magnification, add the DL-UV (#58-947) or LDL-UV (#58-948) Doubler Tube on the C-Mount. Mounting is provided through an included 1/4-20 mounting clamp. A variety of UV lighting options are available including the [MH-100 illuminator](#), [UV curing lamps](#), and [Broadband Fiber Coupled Illuminators](#).

Technical Information

InfiniProbe™ UV Video Microscopes Right Angle Configuration



Units: mm

InfiniProbe™ UV Video Microscopes Standard Configuration

