

InfiniTube FM In-Line Attachment, +10X Objectives

See More by [Infinity Photo-Optical Company](#)



InfiniTube FM In-Line Attachment, +10X Objectives, #58-312

Stock **#58-312** 1 In Stock

-

1

+

€835^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€835,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Lens Accessory	Type:
----------------	-------

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:

- Direct to Video C-Mount for 2/3" and Smaller Sensor Cameras
- Internal Focusing

InfiniTube™ FMSystems are used to mount infinite-conjugate objectives to C-mount cameras, yielding magnifications not possible with ordinary video lenses, such as 50X magnification. The InfiniTube™ system can be configured in a variety of fashions. It can be utilized alone (InfiniTube™ [#58-310](#) or [#58-309](#)) for applications where illumination is provided from another source such as a backlight or directional illumination. The InfiniTube™ FMSystems can also be configured for in-line illumination with attachments. The first in-line attachment ([#58-313](#)) has been designed for high performance with objectives having a magnification of 10X or below and is not suggested for use with higher magnification objectives. The second in-line attachment ([#58-312](#)) has been designed to work with increased efficiency when used with magnifications of 10X or higher, but can be utilized with all magnifications. All in-line attachments accept our [Fiber Optic Light Guides](#) with a 0.312" tip diameter.

Note: **Standard system** for 2/3" sensors still available.

[illegible]

System Includes		Stock No.
InfiniTube In-Line Assembly Unit		#58-311
Hitachi KP-D20B Camera		#55-837
15.1" Diagonal LCD Monitor (US version only)		#56-522
Y-C Cable (6 ft.)		#39-255
Mitutoyo/Achrovid™ Objective Adapter		#58-316
MI-150 Fiber Optic Illuminator		#55-718
Fiber Optic Light Guide (48" L)		#39-367
Fiber Optic Adapter		#38-944
Standard Boom Stand		#54-120
Rack & Pinion Mounting Plate		#54-123
C-Clamp with 1/4-20 Mounting Hole		#57-788