

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Isuzu ISK Colored Glass Heat Absorbing Filters

Stock #15-701 3-4 DAYS



1



€38,00

ADD TO CART

Qty 1-9

€38,00

Qty 10+

€34,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
12.50 ±0.25

Optical Density OD (Average):  
4.51 @ 1064nm

Clear Aperture CA (mm):  
11.25

|                                                                         |
|-------------------------------------------------------------------------|
| <div>Cut-Off Wavelength (nm):<br/>668.00 ±13</div>                      |
| <div>Density (g/cm³):<br/>2.62</div>                                    |
| <div>Glass/Filter Number:<br/>Isuzu ISK167</div>                        |
| <div>Substrate: <input type="checkbox"/><br/>Heat Absorbing Glass</div> |
| <div>Minimum Transmission (%):<br/>≥78 @ 400 - 550nm</div>              |
| <div>Operating Temperature (°C):<br/>300 Maximum</div>                  |
| <div>Coating:<br/>Uncoated</div>                                        |
| <div>Index of Refraction n<sub>d</sub>:<br/>1.52</div>                  |
| <div>Surface Quality:<br/>60-40</div>                                   |
| <div>Transformation Temperature (°C):<br/>597</div>                     |
| <div>Thickness (mm):<br/>3.00 ±0.38</div>                               |
| <div>Type:<br/>IR Cut-Off Filter</div>                                  |
| <div>Parallelism (arcmin):<br/>3</div>                                  |
| <div>Reflection Factor P<sub>d</sub>:<br/>0.92</div>                    |
| <div>Wavelength Range (nm):<br/>300 - 2700</div>                        |
| <div>Surface Flatness (P-V):<br/>3λ</div>                               |

### Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS 2015:<br/><a href="#">Compliant</a></div>             |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |