

Coherent® EnergyMax 1110743 | 25μJ-50mJ, DB25

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock **#66-279** [CONTACT US](#)

- 1 + **€1.760,00**

ADD TO CART

Qty 1+

€1.760,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Active Area Diameter (mm):
25

Connector:
DB25

Model Number:
J-25MB-LE
Coherent Part Number: 1110743

Type:
[Meter required](#)

Type of Sensor: Pyroelectric
Length of Cable (m): 2.5
Linearity (%): ±3
Calibration Uncertainty (%): ±2
Calibration Wavelength (nm): 1064
Noise Equivalent Energy (μJ): <1
Maximum Repetition Rate (pps): 1000
Maximum Incident Beam Power (W): 5
Maximum Pulse Width (μs): 17
Compatible Meters: #35-203 , #66-277 , #88-412
Wavelength Range (nm): 190 - 12000
Maximum Incident Energy Density: 500mJ/cm² (10ns, 1064nm)
Energy Range: 25μJ - 50mJ
Preferred Meter: #66-277

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View