

JAI Go-X, 2402C-PGE, 1/2.3" 2.3MP, GigE Color Camera



Stock #29-147 **1 In Stock**

- 1 + €600⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€600,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Color

Spectrum:

General

Color Camera

Type:

GOX-2402C-PGE

Model Number:

JAI

Manufacturer:

Camera Series:

Physical & Mechanical Properties

29 x 29 x 51.5 **Dimensions (mm):**

65 **Weight (g):**

Full **Housing:**

Sensor

1/2.3" **Sensor Format:**

2.30 **Resolution (Megapixels):**

50.00 **Frame Rate (fps):**

1,920 x 1,200 **Pixels (H x V):**

3.45 x 3.45 **Pixel Size, H x V (µm):**

6.6 x 4.1 **Sensing Area, H x V (mm):**

Sony IMX392 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

8/10/12 Bit **Pixel Depth:**

GigE Vision **Machine Vision Standard:**

Electrical

3.7 **Power Consumption (W):**

Hardware & Interface Connectivity

GigE (PoE) **Interface:**

RJ45 with Screw Locks **Connector:**

Power Supply:
Power Supply Required and Sold Separately.
USA: #29-171
Europe: #29-171
Japan: #29-171
Korea: Not Available
China: Not Available

Hardware Trigger (GPIO) or Software Trigger **Synchronization:**

Back Panel **Interface Port Orientation:**

6-pin Hirose **GPIO Connector Type:**

Threading & Mounting

C-Mount **Mount:**

Environmental & Durability Factors

-5 to +45 **Operating Temperature (°C):**

-25 to +60 **Storage Temperature (°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Up to 12.3 MP Resolution
- USB and GigE Versions Available
- Longest Industry Warranty (6 Years)

JAI® Go-X Series Cameras are designed to be compact, industrial grade, reliable cameras with excellent image quality. Featuring industrial grade shock and vibration ratings (80G/10G) as well as excellent thermal dissipation, these cameras are ideal for factory floors and assembly lines. Designed with a variety of capabilities, these cameras are capable of region-of-interest (ROI), blemish compensation with shading correction, and 8, 10, and 12-bit output. JAI® Go-X Series Cameras are available in resolutions ranging from 2.3 to 12.3MP with both USB or Gigabit Ethernet (GigE) outputs. Downloadable software is [available](#) for both GigE and USB options.
