

[See all 16 Products in Family](#)

JAI Go-X, 2402M-USB, 1/2.3" 2.3MP, USB Monochrom Camera



Stock #29-154 1 In Stock

-

1

+

€700^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€700,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Monochrome	Spectrum:
------------	-----------

General

Monochrome Camera	Type:
-------------------	-------

GOX-2402M-USB	Model Number:
---------------	---------------

JAI	Manufacturer:
-----	---------------

	Camera Series:
--	----------------

Go-X	
Physical & Mechanical Properties	
29 x 29 x 51.5	Dimensions (mm):
65	Weight (g):
Full	Housing:
Sensor	
1/2.3"	Sensor Format:
2.30	Resolution (Megapixels):
162.00	Frame Rate (fps):
1,920 x 1,200	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
6.6 x 4.1	Sensing Area, H x V (mm):
Sony IMX392	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/10/12 Bit	Pixel Depth:
USB3 Vision	Machine Vision Standard:
Electrical	
4.3	Power Consumption (W):
Hardware & Interface Connectivity	
USB 3.1 Gen 1	Interface:
USB 3.1 Gen 1, Micro-B	Connector:
Power Supply Required and Sold Separately. USA: #29-171 Europe: #29-171 Japan: #29-171 Korea: Not Available China: Not Available	Power Supply:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
6-pin Hirose	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
Environmental & Durability Factors	
-5 to +45	Operating Temperature (°C):
-25 to +60	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Up to 12.3 MP Resolution
- USB and GigE Versions Available
- Longest Industry Warranty (6 Years)

JAI® Go-XSeries Cameras are designed to be compact, industrial grade, reliable cameras with excellent image quality. Featuring industrial grade shock and vibration ratings (80G/10G) as well as excellent thermal dissipation, these cameras are ideal for factory floors and assembly lines. Designed with a variety of capabilities, these cameras are capable of region-of-interest (ROI), blemish compensation with shading correction, and 8, 10, and 12-bit output. JAI® Go-XSeries Cameras are available in resolutions ranging from 2.3 to 12.3MP with both USB or Gigabit Ethernet (GigE) outputs. Downloadable software is [available](#) for both GigE and USB options.
