

Hoya L37 (370nm), 25.4mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #66-049 3-4 DAYS

⊖

1

⊕

€44,00

ADD TO CART

Qty 1-10
€44,00

Qty 11+
€39,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40

Cut-Off Position λ_c (nm):
370±6

Cut-On Wavelength (nm):
370.00 ±6

Density (g/cm³): 3.26
Glass/Filter Number: Hoya L37
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Clear
Surface Quality: 80-50
Transformation Temperature (°C): 440
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.38
Reflection Factor P _d : 0.92
Bevel: Protective as needed
Δλ (nm): <35
TH (%): >85

Regulatory Compliance

Reach 181: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View