

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Precision Molded Aspheric Lenses

Stock #19-702 [CONTACT US](#)



1



€78,00

ADD TO CART

Qty 1-10

€78,00

Qty 11+

€67,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
6.65 ±0.015

Effective Focal Length EFL (mm):
6.70 @ 515nm

Numerical Aperture NA:
0.44

Substrate: D-ZK3
Focal Length Tolerance (%): ±1
Coating: BBAR (600-1050nm)
Coating Specification: R _{abs} <1.0% @ 600 - 1050nm
Surface Quality: 60-40
Clear Aperture CA (mm): 5.75
Edge Thickness ET (mm): 1.82
Center Thickness CT (mm): 3.02 ±0.03
f/#: 1.01
Bevel: Protective bevel as needed
Compatible Window: Thickness: 0.25 (t) (mm) Material: BK7
Distance from Window to Lens (D) (mm): 4.25
Lightpath Lens Code: 354525
Operating Temperature (°C): ≤200
Wavelength Range (nm): 600 - 1050
Typical Applications: Collimate or Focus Laser Light
Working Distance (mm): 4.9
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant