

Lumenera INFINITY 2-1R Microscopy Color Camera

See More by [Teledyne DALSA](#)



Teledyne Lumenera INFINITY Microscopy Cameras



Stock #33-272 3-4 DAYS

- 1 +

€2.425,00

ADD TO CART

Qty 1+

€2.425,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
USB 2.0

Type:
Color Microscopy Camera

Manufacturer:
Teledyne Lumenera

Mounting Threads: 2 x ¼-20 (Integrated into Housing)
Image Buffer: Not Specified
Camera Family: INFINITY
Model Number: INFINITY2-1R
Imaging Sensor: Sony ICX205
Type of Sensor: Progressive Scan CCD
Type of Shutter: Global
Camera Sensor Format: 1/2"
Resolution (MegaPixels): 1.40
Pixels (H x V): 1,392 x 1,040
Pixel Size, H x V (µm): 4.65 x 4.65
Sensing Area, H x V (mm): 6.47 x 4.84
Frame Rate (fps): 30.00
Pixel Depth: 8/14 bit
Exposure Time: 48µs - 500ms (video)
Power Supply: Power over USB
Power Consumption (W): 2.5
GPIOs: N/A
Synchronization: N/A
Dimensions (mm): 97.8 x 69.8 x 50.8 (excludes lens mount)
Weight (g): 340
Mount: C-Mount
Housing: Full
Interface Port Orientation: Side Panel
Dynamic Range (dB): 64.6
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -30 to +70
GPIO Connector Type: None

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View