

[See all 8 Products in Family](#)

M30.5 x 0.5 Male to T-Mount Female Step-Up Adapter



M27.0 x 0.5 to T-Mount Step-Up Adapter, #12-481

Stock **#12-482** **16 In Stock**

-

1

+

€34²⁵

ADD TO CART

Volume Pricing	
Qty 1-9	€34,25 each
Qty 10-25	€30,90 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Filter Sold Separately	Note:
Filter Adapter	Type:
Thread Adapter	Function:
Physical & Mechanical Properties	

27.5	Clear Aperture CA (mm):
48.0	Outer Diameter (mm):
8.0	Total Thickness with Thread (mm):
Threading & Mounting	
T-Mount to M30.5 x 0.5	Thread Type:
M42 x 0.75 (T-Mount)	Inner Thread:
5.5	Mount Thickness (mm):
M30.5 x 0.5	Outer Thread:
Regulatory Compliance	
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Integrate C and T-Mount Components into Imaging Systems
 - Compatible with M22.5 to M40.5 Machine Vision Threads
 - Step-Up Design Prevents Vignetting
- Machine Vision Adapters for C and T-Mount Components facilitate integration of various components into imaging systems. Polarizers, beamsplitters, or any other C or T-Mount component can be coupled to a standard machine vision thread via these adapters. Additionally, unmounted optical components including filters can be mounted in our [C-Mount or T-Mount Circular Optic Mounts](#) for easy integration. Compatible machine vision threads range from M22.5 to M40.5. The step-up design prevents vignetting.