

[See all 8 Products in Family](#)

M35.5 x 0.5 Male to T-Mount Female Step-Up Adapter



M27.0 x 0.5 to T-Mount Step-Up Adapter, #12-481

Stock **#12-484** **5 In Stock**

⊖ 1 ⊕ €34²⁵

ADD TO CART

Volume Pricing

Qty 1-9	€34,25 each
Qty 10-25	€30,90 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Filter Sold Separately	Note:
Filter Adapter	Type:
Thread Adapter	Function:

Physical & Mechanical Properties

32.5 Clear Aperture CA (mm):

48.0 Outer Diameter (mm):

8.0 Total Thickness with Thread (mm):

Threading & Mounting

T-Mount to M35.5 x 0.5 Thread Type:

M42 x 0.75 (T-Mount) Inner Thread:

5.5 Mount Thickness (mm):

M35.5 x 0.5 Outer Thread:

Regulatory Compliance

[View](#) Certificate of Conformance:

[Compliant](#) Reach 240:

Product Details

- Integrate C and T-Mount Components into Imaging Systems
- Compatible with M22.5 to M40.5 Machine Vision Threads
- Step-Up Design Prevents Vignetting

Machine Vision Adapters for C and T-Mount Components facilitate integration of various components into imaging systems. Polarizers, beamsplitters, or any other C or T-Mount component can be coupled to a standard machine vision thread via these adapters. Additionally, unmounted optical components including filters can be mounted in our [C-Mount or T-Mount Circular Optic Mounts](#) for easy integration. Compatible machine vision threads range from M22.5 to M40.5. The step-up design prevents vignetting.