

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #49-811 3-4 DAYS



1



€199,00

ADD TO CART

Qty 1-9

€199,00

Qty 10+

€183,60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
33.8

Filter Thread:
M39 x 0.50

Cut-Off Wavelength (nm):
690.00

Cut-On Wavelength (nm):

390.00
Index of Refraction n_d: 1.52 Substrate, Varies by Layer
Note: AR Coating: Both Surfaces Multi-Layer
Outer Diameter (mm): 40.5
Substrate: ☐ Float Glass
Substrate Thickness (mm): 2.0
Surface Quality: 60-40
Thickness with Mount (mm): 6.4
Type: Mounted Imaging Filter

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant