

M46 x 0.75 Mounted IR Cut-Off Filter



Stock #54-744 3-4 DAYS

⊖ 1 ⊕ **€187,00**

ADD TO CART

Qty 1-9
€187,00

Qty 10+
€172,40

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
40.8

Filter Thread:
M46 x 0.75

Cut-Off Wavelength (nm):
750.00

Glass/Filter Number:

[SCHOTT KG3](#)

Index of Refraction n_d :
1.52

Note:
AR Coating: Both Surfaces Multilayer Broadband AR

Outer Diameter (mm):
50.0

Substrate: ☐
[Schott KG-3](#)

Substrate Thickness (mm):
2.0

Surface Quality:
60-40

Thickness with Mount (mm):
7.0

Type:
Mounted Imaging Filter

Wavelength Range (μm):
0.3 - 2.7

Wavelength Range (nm):
300 - 2700

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)
