


Micro Line and Dot Standard Stage Micrometer



Stock **#58-606** 2 In Stock

-

1

+

€845^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€845,00 each
Qty 5+	€803,80 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
No	NIST Certification:
Physical & Mechanical Properties	
2µm, 3µm, 4µm, 5µm, 6µm, 7µm, 8µm, 9µm, 10µm, 25µm, 50µm, 75µm, 100µm	Scale Divisions:
25.4 x 76.2	Dimensions (mm):

1.50 ±0.100	Thickness (mm):
±0.100	Dimensional Tolerance (mm):

Optical Properties

Chrome on Glass	Substrate:
60-40	Surface Quality:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- New Opal Version Available
- Calibrate Pixel Dithering
- Lines and Dot Range from 2µm to 100µm

The Micro Line and Dot Standard is designed to calibrate imaging devices performing critical measurements. The pattern features known dot and line sizes of 2µm, 3µm, 4µm, 5µm, 6µm, 7µm, 8µm, 9µm, 10µm, 25µm, 50µm, 75µm, 100µm. Calibrating with this target can limit the effects of pixel dithering in image processing algorithms. Target is chrome on glass or chrome on opal.