


In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

Microlens Array 10 x 10mm, 300µm Pitch, 1.6° Divergence



Microlens Arrays



Stock #64-476 3-4 DAYS



1



€705,00

ADD TO CART

Qty 1-10

€705,00

Qty 11+

€620,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
5.10

Substrate:
[Fused Silica](#) (Corning 7980)

Coating: Uncoated
Type: Lens Array
Wavelength Range (nm): 200 - 2200
Dimensional Tolerance (mm): ±0.05
Dimensions (mm): 10.0 x 10.0
Divergence Angle (°): ±1.6
Lens Profile: Spherical
Pitch (µm): 300.00
Pitch Tolerance (µm): ±0.25
Radius R (mm): 2.35
Thickness (mm): 1.20
Thickness Tolerance (mm): ±0.05
Type of Optics: Plano-Convex

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View